


1st Brushless ENDO MOTOR

MotoPex Super mini head &Slim neck Stronger power Precise rotation Lowernoise Balances Weight GUILIN WOODPECKER MEDICAL INSTRUMENT CO., LTD.

High performance brushless motor


1 – Adjustable reciprocating angle (10° interval; adjustment range: 20° -400°); Accurate rotating angle reduces risk of instrument fracture and enables higher preparing efficiency.



10° for each unit

2 - Smooth rotation and lower noise make

treatment more endurable for patients.



3- Strong power,

together with accurate and stable torque output, helps to realize efficient root canal preparation.





Brushless Endo Motor=Brush Endo Motor × 10



Built-in over 30 mainstream file system

Speed range: 100-1200 RPM Torque range: 0.4-5.0N.cm

Reciprocating angle adjustment range: 20° -400°



Super Mini Contra-angle

Super mini head with a diameter of 8mm and a height of 9.7mm brings clear vision during operation.





head & neck

Built-in Apex locator

Integrated length determination makes endodontic treatment safer and more efficient. Realize real-time display of file location in canal. Automatically stops or reversely rotates as soon as the file reaches the apical stop, so as to prevent perforation. Auto Start and Auto Stop functions respectively enable motor to automatically start while the file gets in canal and stop when it is out.









2000mAh Lithium battery 360° rotatable contra-angle









The choice of millions of dentists worldwide



Website: www.glwoodpecker.com



EC REP MedNet GmbH
Borkstrasse 10·48163 Muenster · Germany



